


RECOMMENDED PANEL CUTOUT  
MAX. PANEL THICKNESS 4mm





| SWITCH FUNCTION |        |
|-----------------|--------|
| POS. 1          | POS. 2 |
|                 |        |
| OFF             | (ON)   |
| OPEN            | 1-2    |

(ON) = MOMENTARY



## NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X =  $\pm 0.4$   
X.XX =  $\pm 0.25$
3. TERMINAL NUMBERS FOR REF ONLY
- ▲ 4. CONTACT MATERIAL: GOLD PLATED
5. RATING: 2A @ 36VDC
6. ELECTRICAL LIFE: 200,000 CYCLES
7. CONTACT RESISTANCE: 50 m $\Omega$  MAX. @ 1A 12VDC (INITIAL)
8. INSULATION RESISTANCE: 1,000 M $\Omega$  MIN. @ 500VDC
9. DIELECTRIC STRENGTH: 2,000 VAC rms.
10. OPERATING TEMPERATURE: -40°C to +85°C
11. PANEL THICKNESS MAX: 4.0mm
12. INGRESS PROTECTION: IP65
13. ▲ DENOTES CRITICAL PARAMETER.
- ▲ 14. HARDWARE INCLUDED: O-RING and HEXNUT (NOT SHOWN)



| REV | ECO NO     | DESCRIPTION  | DATE     | BY |  <b>E-SWITCH®</b> |                 |        |                   | OBJECT ID |
|-----|------------|--------------|----------|----|--------------------------------------------------------------------------------------------------------|-----------------|--------|-------------------|-----------|
| B   | ECO-103053 | Print update | 11/12/24 | MW |                                                                                                        |                 |        |                   | 000002798 |
|     |            |              |          |    | TITLE PV5S24018G                                                                                       |                 |        |                   |           |
|     |            |              |          |    | SCALE 2:1                                                                                              | DATE 10/17/2017 | DR MJR | DWG 52-PV5S24018G | REV B     |

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO  
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED