



$\varnothing 12.00^{+.20}_{-.00}$
 $[\text{.472}^{+.008}_{-.000} \text{ in}]$




PANEL MOUNTING
 MAX. PANEL THICKNESS 4mm



SWITCH FUNCTION	
POS. 1	POS. 2
OFF	(ON)
OPEN	1-2

(ON) = MOMENTARY





▲ **CIRCUIT: SPST**

▲ **DOMED**
 ACTUATOR COLOR:
 STAINLESS STEEL


▲ **BODY COLOR:**
 STAINLESS STEEL

M12x1.0
 THREAD



NOTE:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: X.X=±0.4
 X.XX=±0.25
- TERMINAL NUMBERS FOR REF ONLY
- ▲ CONTACT MATERIAL: SILVER
- RATING: 2A @ 36 VDC
- ELECTRICAL LIFE: 200,000 CYCLES
- CONTACT RESISTANCE: 50 mΩ MAX. @ 1A 12VDC (INITIAL)
- INSULATION RESISTANCE: 1,000 MΩ MIN. @ 500VDC.
- DIELECTRIC STRENGTH: 2,000 VAC rms.
- OPERATING TEMPERATURE: -40°C TO +85°C.
- PANEL THICKNESS MAX: 4.0 mm.
- INGRESS PROTECTION: IP65
- ▲ DENOTES CRITICAL PARAMETER.
- ▲ 14. HARDWARE INCLUDED, 1 O-RING & 1 HEX NUT.(NOT SHOWN)



REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
C	ECO-103847	PRINT UPDATE	01/06/26	JS	TITLE PV5S640SS				000002816
					SCALE	DATE	DR	DWG	REV
					2:1	8/5/2009	EBP	52-PV5S640SS	C

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO
 E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED