


RECOMMENDED PANEL CUTOUT  
MAX. PANEL THICKNESS 12mm




▲ SWITCH FUNCTION

| POS. 1            | POS. 2            |
|-------------------|-------------------|
|                   |                   |
| 1-2 ON<br>3-4 OFF | 1-2 OFF<br>3-4 ON |



## NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4  
X.XX = ± 0.25
3. TERMINAL NUMBERS FOR REF. ONLY
4. RATING: 2A @ 48VDC
5. ILLUMINATION VOLTAGE: 12V
6. CONTACT RESISTANCE: 50mΩ MAX. @ 1A 12VDC
7. INSULATION RESISTANCE: 1,000MΩ @ 500VDC
8. DIELECTRIC STRENGTH: 2,000VAC MIN. FOR 1 MINUTE
9. ELECTRICAL LIFE: 50,000 CYCLES
10. OPERATING TEMPERATURE: -20°C to 55°C
11. INGRESS PROTECTION: IP65
12. SUPPLIED HARDWARE: O-RING AND HEXNUT
13. ▲ DENOTES CRITICAL PARAMETER



|     |        |                                        |        |    |
|-----|--------|----------------------------------------|--------|----|
| B   | 23960  | ON (OFF) / OFF (ON) to ON-OFF / OFF-ON | 7/9/19 | MW |
| A   | 23957  | RELEASE FOR PRODUCTION                 | 7/2/19 | MW |
| REV | PCR NO | DESCRIPTION                            | DATE   | BY |

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY  
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE PV7F2T011-3L4

SCALE 1:1

DATE 7/2/2019

DR MW

DWG 52-PV7F2T0113L4

REV B