







O.P. (MM)	P.T. (MM)
14.9 ± 1.0	4.0 MAX

O.P. = OPERATING POINT
P.T. = PRE-TRAVEL



NOTES:

1. ALL DIMENSIONS IN MM [INCH] Ø2.50
2. GENERAL TOLERANCE: X.X=± 0.4 [.098 in]
X.XX=± 0.25
3. RATING: 0.4VA @20VAC OR DC 1.85
▲ 4. OPERATING FORCE: 65± 20 GRAMS [.073 in]
5. OPERATING TEMP: -25°C TO 85°C
6. ELECTRICAL LIFE: 50,000 CYCLES MIN. 8
7. MECHANICAL LIFE: 1,000,000 CYCLES TYP. [.34
8. INSULATION RESISTANCE: 100 MEGA-OHMS
9. DIELECTRIC STRENGTH: 1000VAC 1 MINUTE (INITIAL VALUE)
10. CONTACT RESISTANCE: 100 mΩ MAX.
▲ 11. CONTACTS: 10 MICRO INCHES MINIMUM GOLD PLATING (PN: Q990001)
12. ▲ DENOTES CRITICAL PARAMETER.

REV	ECO NO	DESCRIPTION	DATE	BY	 E-SWITCH®					OBJECT ID
B	ECO-100798	REMOVE VDE RATING AND LOGO	03/23/22	JS						000021280
					TITLE MS085R105F065S1A					
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED					SCALE 2:1	DATE 6/12/2014	DR EBP	DWG Q970144	REV B	