





NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X $\pm$ 0.4
X.XX $\pm$ 0.25
3. TERM. NOS. FOR REFERENCE ONLY.
4. RATING 0.1A @30V DC
- ▲5. MATERIALS:
CONTACT/TERMINALS: SILVER PLATE
HOUSING: PBT UL94V0
BASE: PA66 UL94V0
ACTUATOR: PA66 UL94V0
6. CONTACT RESISTANCE: 100 m Ω (INITIAL)
- ▲7. TIMING: NON-SHORTING
8. OPERATING FORCE: 280 $\pm$ 50GF
9. TRAVEL: LATCHING
2MM TO LOCK
3MM OVERALL
10. ELECTRICAL LIFE: 10000 CYCLES
11. OPERATING TEMP: -20°C TO +70°C
12. ▲DENOTES CRITICAL PARAMETER.
13. 2002/95/EC (ROHS) COMPLIANT



C	19753	CHANGE DIMENSION POINT TO BRACKET	3/10/11	BGL
B	19671	CIRCUIT DIAGRAM & DIM CHANGES	2/10/11	BGL
A	16489	RELEASED FOR PRODUCTION	9/28/2006	TN
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED



TITLE PBH4UEEKZXNAGV

SCALE 2.5:1

DATE 9/28/2006

DR TN

DWG Q960020

REV C