




▲ SWITCH FUNCTION


POS. 1	POS. 2
OFF	(ON)
OPEN	1-2

(ON) = MOMENTARY



NOTE:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
- TERMINAL NOS. FOR REF. ONLY
- RATING: 2A @ 36VDC
- CONTACT RESISTANCE: 50m Ω MAX. @ 1A 12VDC
- INSULATION RESISTANCE: 100M Ω @ 500VDC
- DIELECTRIC STRENGTH: 1,500V, RMS 50Hz, 1min
- ELECTRICAL LIFE: 200,000 CYCLES
9. CONTACT MATERIAL: SILVER
- OPERATING TEMPERATURE: -40°C to 85°C
- INGRESS PROTECTION: IP67
- LED VOLTAGE: BASE VOLTAGE 2.8V TYP.
- ▲ DENOTES CRITICAL PARAMETER
- HARDWARE INCLUDED: HEX NUT AND O-RING (NOT SHOWN)



REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
E	ECO-102762	Print update	07/03/24	MW	TITLE PV0H24011-231				000002281
					SCALE	DATE	DR	DWG	REV
					2:1	11/17/2016	MW	52-PV0H24011231	E

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED