



SWITCH FUNCTION	
POS. 1	POS. 2
OFF	(ON)
OPEN	1-2

(ON) = MOMENTARY



- NOTE:
- ALL DIMENSIONS IN MM [INCH]
  - GENERAL TOLERANCE: X.X =  $\pm 0.4$   
X.XX =  $\pm 0.25$
  - TERMINAL NUMBERS FOR REF. ONLY
  - RATING: 2A @ 36VDC
  - CONTACT RESISTANCE: 50m $\Omega$  MAX. @ 1A 12VDC
  - INSULATION RESISTANCE: 1,000M $\Omega$  @ 500VDC
  - DIELECTRIC STRENGTH: 2,000VAC MIN. FOR 1 MINUTE
  - ELECTRICAL LIFE: 200,000 CYCLES
  - CONTACT MATERIAL: SILVER PLATED COPPER
  - OPERATING TEMPERATURE: -20°C to 55°C
  - INGRESS PROTECTION: IP65
  - ▲ DENOTES CRITICAL PARAMETER
  - ▲ 13. HARDWARE INCLUDED: HEX NUT AND O-RING (NOT SHOWN)



A	23538	NEW RELEASE	8/24/18	MW
REV	PCR NO	DESCRIPTION	DATE	BY

TITLE PV1S240SS-M01				
SCALE	DATE	DR	DWG	REV
2:1	8/24/2018	MW	52-PV1S240SSM01	A

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED