



PANEL MOUNTING
MAX. PANEL THICKNESS 8.0mm



▲ DOMED ACTUATOR
POLISHED
STAINLESS STEEL



▲ CIRCUIT: SPST


| SWITCH FUNCTION | |
|-----------------|--------|
| POS. 1 | POS. 2 |
| OFF | (ON) |
| OPEN | 1-2 |

(ON) = MOMENTARY

3.6 ± .50
[.14 ± .02 in]

2.0
[.08 in]

M19x1.0




▲ BODY FINISH
POLISHED
STAINLESS STEEL

▲ 18.0 ± .50
[.71 ± .02 in]

▲ 25.3 ± .50
[1.00 ± .02 in]

11.30
[.445 in]

.50
[.020 in]



24.0 ± .50
[.94 ± .02 in]

2.80
[.110 in]

NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERMINAL NOS. FOR REF. ONLY
- ▲ 4. FUNCTION: SPST
- ▲ 5. RATING: 2A @ 36VDC
6. CONTACT RESISTANCE: 50mΩ MAX. @ 1A 12VDC
7. INSULATION RESISTANCE: 1,000MΩ @ 500VDC
8. DIELECTRIC STRENGTH: 2,000VAC MIN. FOR 1 MINUTE
9. ELECTRICAL LIFE: 200,000 CYCLES
10. CONTACT MATERIAL: SILVER PLATED COPPER
11. OPERATING TEMPERATURE: -20°C TO 55°C
12. INGRESS PROTECTION: IP65
13. ▲ DENOTES CRITICAL PARAMETER
- ▲ 14. HARDWARE INCLUDED: HEX NUT AND O-RING (NOT SHOWN)



OBJECT ID
000002360

| | | | | |
|-----|--------|------------------------------|---------|-----|
| B | 23591 | UPDATED RATING TO 2A @ 36VDC | 10/5/18 | MJR |
| A | 22304 | NEW RELEASE | 5/11/16 | MJR |
| REV | PCR NO | DESCRIPTION | DATE | BY |

TITLE PV1S240SS

| | | | | |
|--------------|-------------------|-----------|---------------------|----------|
| SCALE 2:1 | DATE 5/11/2016 | DR MJR | DWG 52-PV1S240SS | REV B |
|--------------|-------------------|-----------|---------------------|----------|

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED