






PANEL CUTOUT
MAX. PANEL THICKNESS 12mm



▲ SPDT ON-OFF / OFF-ON
CONTACT CONFIGURATION



NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERMINAL NOS. FOR REF. ONLY
4. RATING: 2A @ 48VDC
5. CONTACT RESISTANCE: 50mΩ MAX. @ 1A 12VDC
6. INSULATION RESISTANCE: 1,000MΩ @ 500VDC
7. DIELECTRIC STRENGTH: 2,000VAC MIN. FOR 1 MINUTE
8. ELECTRICAL LIFE: 50,000 CYCLES
9. OPERATING TEMPERATURE: -20°C TO 70°C
10. INGRESS PROTECTION: IP65
11. ▲ DENOTES CRITICAL PARAMETER
12. ILLUMINATION COLOR: WHITE
- ▲ 13. ILLUMINATION VOLTAGE: 6V
- ▲ 14. SUPPLIED HARDWARE: O-RING AND HEX NUT

REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
D	ECO-102085	PRINT UPDATE	07/10/23	JS	TITLE PV8F2T0SS-303				000003067
					SCALE	DATE	DR	DWG	REV
					1:1	9/9/2009	CAB	52-PV8F2T0SS303	D

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED