




ADAPTER	WIRE	LENGTH
SW1-1	WIRE, 24 AWG AWM UL1061, BLACK	150.0 [5.9 in]
SW1-2	WIRE, 24 AWG AWM UL1061, BLACK	150.0 [5.9 in]




## LED SCHEMATIC



▲ ILLUMINATION  
COLOR: GREEN

▲ BODY FINISH:  
BLACK



**NOTE:**

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X =  $\pm 0.4$   
X.XX =  $\pm 0.25$
3. TERMINAL NUMBERS FOR REF ONLY
4. OPERATING TEMP:  $-40^{\circ}\text{C}$  to  $85^{\circ}\text{C}$
5. CURRENT RATING: 2mA-20mA
6. LAMP VOLTAGE: 2.8V
7. IP RATING: IP67
8. ▲ DENOTES CRITICAL PARAMETER.
9. HARDWARE SUPPLIED: O-RING AND HEXNUT

REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®	OBJECT ID
D	ECO-103573	CORRECT PANEL DIM	08/05/25	JS		000003256
					TITLE	PVL06FW131
					SCALE	3:2
					DATE	9/12/2019
					DR	MJR
					DWG	52-PVL06FW131
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED					REV	D