





SWITCH FUNCTION	
POS. 1	POS. 2
OFF	(ON)
None	1-2
( ) = MOMENTARY	



NOTE:  
1. ALL DIMENSIONS IN MM [INCH]  
2. GENERAL TOLERANCE: X.X =  $\pm 0.4$   
X.XX =  $\pm 0.25$   
3. TERMINAL NUMBERS FOR REF ONLY  
4. CONTACT MATERIAL: Silver  
5. RATING: 50mA 24VDC  
6. ELECTRIC LIFE: 500,000 MAKE-AND-BREAK CYCLES  
AT FULL LOAD.  
7. INSULATION RESISTANCE: 1000 M $\Omega$  MIN.  
8. DIELECTRIC STRENGTH: 250 VAC MIN. FOR 1 MINUTE  
9. CONTACT RESISTANCE: 100m $\Omega$  MAX.  
10. OPERATING TEMP.: -40°C to +85°C  
11. TRAVEL: 0.5mm  
12. ▲ DENOTES CRITICAL PARAMETER.  
13. INGRESS PROTECTION: IP65  
▲ 14. LED VOLTAGE: 2.8V  
15. HARDWARE SUPPLIED: O-RING AND HEXNUT

REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®			OBJECT ID
D	ECO-103542	PRINT UPDATE	07/25/25	JS				000003331
					TITLE PVT4FS4SS331			
					SCALE 3:2			
		THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED	DATE	DR	DWG	52-PVT4FS4SS331	REV	D
			3/19/2018	RC				