





| SWITCH FUNCTION |        |
|-----------------|--------|
| POS. 1          | POS. 2 |
|                 |        |
| OFF             | (ON)   |
| None            | 1-2    |

( ) = MOMENTARY



## NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X =  $\pm 0.4$   
X.XX =  $\pm 0.25$
3. TERMINAL NUMBERS FOR REF ONLY
4. CONTACT MATERIAL: Silver
5. RATING: 50mA 24VDC
6. ELECTRIC LIFE: 500,000 MAKE-AND-BREAK CYCLES AT FULL LOAD.
7. INSULATION RESISTANCE: 1000 M $\Omega$  MIN.
8. DIELECTRIC STRENGTH: 250 VAC MIN. FOR 1 MINUTE
9. CONTACT RESISTANCE: 100m $\Omega$  MAX.
10. OPERATING TEMP.: -40°C to +85°C
11. TRAVEL: 0.5mm
12. ▲ DENOTES CRITICAL PARAMETER.
13. INGRESS PROTECTION: IP65
- ▲ 14. LED VOLTAGE: 24V
15. HARDWARE SUPPLIED: O-RING AND HEXNUT



| REV | ECO NO     | DESCRIPTION  | DATE     | BY | E-SWITCH®          |                 |       |                     | OBJECT ID |
|-----|------------|--------------|----------|----|--------------------|-----------------|-------|---------------------|-----------|
| B   | ECO-103542 | PRINT UPDATE | 07/25/25 | JS | TITLE PVT4FS4SS335 |                 |       |                     | 100119783 |
|     |            |              |          |    | SCALE 3:2          | DATE 10/15/2021 | DR JS | DWG 52-PVT4FS4SS335 | REV B     |

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED