



RECOMMENDED PANEL CUTOUT
MAX. PANEL THICKNESS
11.0 [.43 in]






SWITCH FUNCTION	
POS. 1	POS. 2
ON	ON

1-3, 4-6 1-2, 4-5



GREEN (REVERSE)
(+) O (-)
GREEN (FORWARD)

▲ DPDT
CONTACT CONFIGURATION



NOTE:
1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERMINAL NUMBERS FOR REF ONLY
▲ 4. CONTACT MATERIAL: SILVER
5. RATING: 2A 24VDC
6. ELECTRIC LIFE: 50,000 MAKE-AND-BREAK CYCLES AT FULL LOAD.
7. INSULATION RESISTANCE: 1,000 MΩ MIN.
8. DIELECTRIC STRENGTH: 2,000 VAC MIN. FOR 1 MINUTE
9. CONTACT RESISTANCE: 50mΩ MAX. @ 1A 12VDC
10. OPERATING TEMP.: -40°C TO 85°C
11. TRAVEL: 2.8 [.11 in]
12. ▲ DENOTES CRITICAL PARAMETER
13. INGRESS PROTECTION: IP67
▲ 14. HARDWARE SUPPLIED: O-RING AND HEXNUT
▲ 15. ILLUMINATION VOLTAGE: 2.8V

REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®			OBJECT ID
C	ECO-103867	PV4 SERIES UPDATE	01/14/26	MR				000002651
					TITLE PV4F2G0SS-331			
					SCALE 1:1			
		THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED			DATE	7/9/2010	DR	DWG
							EBP	52-PV4F2G0SS331
					REV	C		