


PANEL CUTOUT





PANEL THICKNESS	(x)
0.75 - 1.25	30.0
1.25 - 2.00	30.4
2.00 - 3.00	30.7

SWITCH FUNCTION	
POS. 1	POS. 2
OFF	ON
NONE	2-1



NOTE:

1. DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERMINAL NUMBERS FOR REF ONLY
- ▲ 4. CONTACT MATERIAL: SILVER
- ▲ 5. CONTACT RATINGS:
ANSI/UL 61058-1
20A @ 125VAC T105 [cURus]
3/4HP T105[cURus]
6. CONTACT RESISTANCE: 35m Ω MAX. @ 50VAC INITIAL
7. INSULATION RESISTANCE: 100M Ω MIN. @ 500VDC
8. DIELECTRIC STRENGTH: 1,500VAC FOR 1 MINUTE
9. ELECTRICAL LIFE: 10,000 CYCLES [cURus]
10. OPERATING TEMPERATURE: -20°C to 105°C [cURus]
- ▲ 11. ILLUMINATION VOLTAGE: 12V LED
12. ▲ DENOTES CRITICAL PARAMETER



REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
H	ECO-102881	NOTE 5 20A WAS 15A NOTE 10 105C WAS 85C	07/30/24	JS	TITLE RB141C1100-214				000001460
					SCALE	DATE	DR	DWG	REV
					1:1	5/3/2011	MW	38-RB141C1100214	H

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED