


**RECOMMENDED PANEL CUTOUT
MAX. PANEL THICKNESS
11.0 [.43 in]**



SWITCH FUNCTION	
POS. 1	POS. 2
	
1-2 ON 3-4 OFF	1-2 (OFF) 3-4 (ON)

() = MOMENTARY






3 ○ ○ 4

▲ SPDT

CONTACT CONFIGURATION

NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERMINAL NUMBERS FOR REF ONLY
4. CONTACT MATERIAL: SILVER
5. RATING: 2A 24VDC
6. ELECTRIC LIFE: 50,000 MAKE-AND-BREAK CYCLES AT FULL LOAD.
7. INSULATION RESISTANCE: 1,000 M Ω MIN.
8. DIELECTRIC STRENGTH: 2,000 VAC MIN. FOR 1 MINUTE
9. CONTACT RESISTANCE: 50m Ω MAX. @ 1A 12VDC
10. OPERATING TEMP.: -40°C TO 85°C
11. TRAVEL: 2.8 [.11 in]
12. ▲ DENOTES CRITICAL PARAMETER
13. LAMP VOLTAGE: 12V
14. INGRESS PROTECTION: IP65
15. HARDWARE SUPPLIED: O-RING AND HEXNUT



REV	ECO NO	DESCRIPTION	DATE	BY	 E-SWITCH®		OBJECT ID
D	ECO-103877	PV4 SERIES UPDATE	01/13/26	MR	TITLE		000002714
					PV4F2Y0SS-3G4		
					SCALE		
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED				1:1	DATE	12/7/2009	DR
				CAB	DWG	52-PV4F2Y0SS3G4	REV
							D