






RECOMMENDED PANEL CUTOUT  
PANEL THICKNESS 1-10mm



▲ SCHEMATIC  
ON-ON  
SPDT ILLUMINATED



## NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ±0.4  
X.XX = ±0.25
3. RATING: 15A @125/250VAC
4. OPERATING FORCE: 3.5 ±1.5N
5. OPERATING TEMP: -25°C to 85°C
6. ELECTRICAL LIFE: 10,000 CYCLES MIN.
7. MECHANICAL LIFE: 1,000,000 CYCLES TYP.
8. INSULATION RESISTANCE: 100 MEGA-OHMS MIN.
9. DIELECTRIC STRENGTH: 1500VAC 1 MINUTE (INITIAL VALUE)
10. CONTACT RESISTANCE: 100 MILLI-OHMS MAX.
11. ▲ DENOTES CRITICAL PARAMETER.
- ▲ 12. LAMP VOLTAGE: 3V
13. TRAVEL: 3.2mm
14. HEX NUT TORQUE: 1-3Nm
15. INGRESS PROTECTION: IP67
- ▲ 16. HARDWARE SUPPLIED: O-RING and HEXNUT

| REV | ECO NO     | DESCRIPTION | DATE     | BY | E-SWITCH®          |          |    |         | OBJECT ID |
|-----|------------|-------------|----------|----|--------------------|----------|----|---------|-----------|
| A   | ECO-101549 | Release     | 01/11/23 | MW | TITLE SAV8F13SS641 |          |    |         | 100123406 |
|     |            |             |          |    | SCALE              | DATE     | DR | DWG     | REV       |
|     |            |             |          |    | 1:1                | 1/5/2023 | MW | T958011 | A         |

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO  
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED