




PANEL MOUNTING





O.P. (MM)	P.T. (MM)
7.0 ±0.2	0.35

O.P. = OPERATING POINT
P.T. = PRE-TRAVEL



NOTES:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: X.X = ±0.4
X.XX = ±0.25
- ▲ 3. RATING: 3A @125VAC
1.5A @250VAC UL
- OPERATING FORCE: 70±25 GRAMS
- OPERATING TEMP: -25°C TO 75°C
- ELECTRICAL LIFE: 10,000 CYCLES MIN.
- MECHANICAL LIFE: 1,000,000 CYCLES
- INSULATION RESISTANCE: 100 MEGA-OHMS MIN.
- DIELECTRIC STRENGTH: 500VAC - 1 MINUTE
- ▲ DENOTES CRITICAL PARAMETER.
- PACKAGED IN TRAYS, 200 PIECES PER TRAY



REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
E	ECO-102005	PRINT UPDATE	06/16/23	JS	TITLE SS0750300F070S1A				000021318
					SCALE	DATE	DR	DWG	REV
					4:1	10/2/2008	BLR	Q971002	E

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED