






P.C. MOUNTING

ISOMETRIC
SCALE: 3:1

O.P. (MM)	P.T. (MM)
10.8 ± 0.8	2.0 Max.

O.P. = OPERATING POINT
P.T. = PRE-TRAVEL



NOTES:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: X.X=± 0.4
X.XX=± 0.25
- 3.** RATING: 3A @125VAC
1.5A @250 VAC UL
- 4.** OPERATING FORCE: 15± 5 GRAMS
- OPERATING TEMP: -25°C TO 75°C
- ELECTRICAL LIFE: 10,000 CYCLES MIN.
- INSULATION RESISTANCE: 100 MEGA-OHMS MIN.
- DIELECTRIC STRENGTH: 500VAC - 1 MINUTE
- ▲ DENOTES CRITICAL PARAMETER.
- 2002/95/EC (ROHS) COMPLIANT
- PACKAGED IN TRAYS, 120 PIECES PER TRAY



A	20304	RELEASE FOR PRODUCTION	11/23/11	BMA
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE SS0750302F015V1A

SCALE 4:1

DATE 11/23/2011

DR BMA

DWG Q971031

REV A