


P.C. MOUNTING







CIRCUIT: SPDT

O.P. (MM)	P.T. (MM)
9.65 ± 0.8	1.35 MAX.

O.P. = OPERATING POINT
P.T. = PRE-TRAVEL

NOTES:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
- ▲ 3. RATING: 3A @125VAC
1.5A @250VAC UL
- OPERATING FORCE: 50 ± 15 GRAMS
- OPERATING TEMP: -25°C TO +75°C
- ELECTRICAL LIFE: 10,000 CYCLES MIN.
- INSULATION RESISTANCE: 100 Mega-OHMS MIN AT 500VDC.
- DIELECTRIC STRENGTH: 1500VAC - 1 MINUTE
- CONTACT RESISTANCE: 100 Milli-OHMS MAX.
- ▲ DENOTES CRITICAL PARAMETER.
- PACKAGED IN TRAYS, 120 PIECES PER TRAY.
- 2002/95/EC (ROHS) COMPLIANT

ISOMETRIC
SCALE: 3:1

TITLE SS0750303F050V2A

A	20701	RELEASE FOR PRODUCTION	8/7/12	RC
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

SCALE	DATE	DR	DWG	REV
4:1	8/7/2012	RC	Q971036	A