


PANEL MOUNTING
MAX. PANEL THICKNESS 4mm




▲ RAISED
ACTUATOR COLOR:
STAINLESS STEEL



SWITCH FUNCTION	
POS. 1	POS. 2
OFF	(ON)
OPEN	1-2



(ON) = MOMENTARY



▲ CIRCUIT: SPST


▲ BODY COLOR:
STAINLESS STEEL

M12x1.0
THREAD



NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERMINAL NUMBERS FOR REF ONLY
- ▲ 4. CONTACT MATERIAL: SILVER
5. RATING: 2A @ 36 VDC
6. ELECTRICAL LIFE: 200,000 CYCLES
7. CONTACT RESISTANCE: 50 mΩ MAX. @ 1A 12VDC (INITIAL)
8. INSULATION RESISTANCE: 1,000 MΩ MIN. @ 500VDC.
9. DIELECTRIC STRENGTH: 2,000 VAC rms.
10. OPERATING TEMPERATURE: -20°C TO +70°C.
11. PANEL THICKNESS MAX: 4.0 mm.
12. INGRESS PROTECTION: IP65
13. ▲ DENOTES CRITICAL PARAMETER.
14. 2011/65/EU (ROHS) COMPLIANT
- ▲ 15. HARDWARE INCLUDED, 1 O-RING & 1 HEX NUT.(NOT SHOWN)



E-SWITCH®

B	22667	UPDATED ACTUATOR	1/9/17	MJR
A	21254	RELEASE FOR PRODUCTION	10/11/13	EBP
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE PV5H240SS

SCALE
2:1

DATE
10/11/2013

DR
EBP

DWG
52-PV5H240SS

REV
B