






PANEL MOUNTING



O.P. (MM)	P.T. (MM)
7.0 ±0.2	0.35

O.P. = OPERATING POINT
P.T. = PRE-TRAVEL



NOTES:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
- ▲ 3. RATING: 0.4VA MAX. @ 20VDC MAX.
- CONTACT RESISTANCE: 100 Milli-OHMS MAX.
- OPERATING FORCE: 130 ± 40 GRAMS
- OPERATING TEMP: -25°C TO 75°C
- ELECTRICAL LIFE: 10,000 CYCLES MIN.
- INSULATION RESISTANCE: 100 MEGA-OHMS MIN.
- DIELECTRIC STRENGTH: 1,500VAC - 1 MINUTE
- ▲ DENOTES CRITICAL PARAMETER.
- PACKAGED IN TRAYS, 200 PIECES PER TRAY

REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
B	ECO-102032	PRINT UPDATE	07/03/23	JS	TITLE SS075R100F130S1A				000021343
					SCALE	DATE	DR	DWG	REV
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED					4:1	9/29/2009	BLR	Q971027	B