


PANEL MOUNTING
MAX. PANEL THICKNESS 4mm

SWITCH FUNCTION	
POS. 1	POS. 2
OFF	(ON)
OPEN	1-2

(ON) = MOMENTARY



▲ CIRCUIT: SPST

▲ DOMED
ACTUATOR COLOR:
YELLOW

▲ BODY COLOR:
STAINLESS STEEL


M12x1.0
THREAD

.50
[.020 in]

6.50
[.256 in]

.80
[.031 in]

9.2±1.0
[.36±.04 in]



Ø17.50
[.689 in]

Ø12.60
[.496 in]



7.2±1.0
[.28±.04 in]

12.9±1.0
[.51±.04 in]

5.10
[.201 in]

4.20
[.165 in]

2.00
[.079 in]

NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERMINAL NUMBERS FOR REF ONLY
4. CONTACT MATERIAL: SILVER
5. RATING: 2A @ 36 VDC
6. ELECTRICAL LIFE: 200,000 CYCLES
7. CONTACT RESISTANCE: 50 mΩ MAX. @ 1A 12VDC (INITIAL)
8. INSULATION RESISTANCE: 1,000 MΩ MIN. @ 500VDC.
9. DIELECTRIC STRENGTH: 2,000 VAC rms.
10. OPERATING TEMPERATURE: -20°C TO +70°C.
11. PANEL THICKNESS MAX: 4.0 mm.
12. INGRESS PROTECTION: IP65
13. ▲ DENOTES CRITICAL PARAMETER.
14. 2011/65/EU (ROHS) COMPLIANT
15. ▲ HARDWARE INCLUDED, 1 O-RING & 1 HEX NUT.(NOT SHOWN)



E-SWITCH®

B	22670	UPDATED ACTUATOR	1/9/17	MJR
A	21435	RELEASE FOR PRODUCTION	4/15/12	EBP
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE PV5S240S6

SCALE

2:1

DATE

4/15/2014

DR

EBP

DWG

52-PV5S240S6

REV

B