




RECOMMENDED
PANEL CUT OUT

▲ SWITCH FUNCTION		
POS. 1	POS. 2	POS. 3
OFF	N/A	ON
OPEN	N/A	1-3

NOTES:

- ALL DIMENSIONS IN MM
- GENERAL TOLERANCE: X.X = ± 0.5
X.XX = ± 0.25
- TERM. NOS. FOR REFERENCE ONLY
- ELECTRICAL LIFE: 6,000 CYCLES
- OPERATING TEMP: 0°C to 85°C
- CONTACT RESISTANCE: 50mΩ MAX. INITIAL
- INSULATION RESISTANCE: 2MΩ AT 500VDC
- DIELECTRIC STRENGTH: 1000VAC FOR 1 MINUTE
- ▲ DENOTES CRITICAL PARAMETER
- CONTACT RATING: 20A 125VAC,
15A 277VAC
2HP 125/277VAC
- SUPPLIED HARDWARE: 2 HEXNUTS


 $\phi 6.00$
[$\phi .236$ in]
▲ 15/32-32UNC
(HARDWARE
NOT SHOWN)

REV	ECO NO	DESCRIPTION	DATE	BY					OBJECT ID
A	ECO-101399	Release	11/11/22	MW	TITLE ST141D12				100123064
					SCALE 1:1	DATE 11/10/2022	DR MW	DWG 34-ST141D12	REV A

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED