



CIRCUIT: SPST



NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERMINAL NUMBERS FOR REF. ONLY
- ▲ 4. CONTACT RATING: 50mA @ 12VDC
5. TRAVEL: 0.30 $\pm$ 0.15mm
- ▲ 6. OPERATING FORCE: 260 $\pm$ 50mN
7. CONTACT RESISTANCE: 100m Ω MAX.
8. ELECTRICAL LIFE: 100,000 CYCLES
9. ▲ DENOTES CRITICAL PARAMETER
10. 2011/65/EU (ROHS) COMPLIANT
11. CONTACT MATERIAL: SILVER
- ▲ 12. PACKAGE: 450 PIECES PER POLYBAG



A	22558	RELEASED FOR PRODUCTION	10/21/16	MW	TITLE TL1100FF260Q				
REV	PCR NO	DESCRIPTION	DATE	BY					
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED					SCALE 2:1	DATE 10/21/2016	DR MW	DWG P001180	REV A