




ACTUATOR
COLOR: BLACK



- NOTES:
1. ALL DIMENSIONS IN MM
 2. GENERAL TOLERANCE: X.X = ±0.4
X.XX = ±0.25
 3. TERM. NOS. FOR REFERENCE ONLY.
 4. RATING: 12VDC, 50mA
 - ▲ 5. OPERATING FORCE: 160 ±50 gf
 6. TRAVEL: 0.25 +0.2/-0.1 mm
 7. CONTACT RESISTANCE: 50 MILLI OHMS MAX. (INITIAL)
 8. MECHANICAL/ELECTRICAL LIFE 100,000 CYCLES MIN.
 - ▲ 9. CONTACT MATERIAL: GOLD
 10. ▲ DENOTES CRITICAL PARAMETER
 11. OPERATING TEMP: -40°C TO 85°C



F	24550	REMOVE STEP IN HOUSING, CHANGE TEMP	10/19/20	JM
E	22850	ADD 3.70 TERMINAL DIM.	5/30/17	MW
D	22235	BLACK ACTUATOR	4/1/16	MW
C	18677	LEG TOLERANCE WAS +/- 0.1	10/9/9	BLR
B	16112	ADD GOLD DOME NOTE	6/6/06	CT
REV	PCR NO	DESCRIPTION	DATE	BY



TITLE TL1105WF160R

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

SCALE	DATE	DR	DWG	REV
4:1	10/9/2009	BLR	P020225	F