




PCB LAYOUT



SCHEMATIC



- NOTES:
1. ALL DIMENSIONS IN MM [INCH]
 2. GENERAL TOLERANCE: X.X=±0.4mm
X.XX=±0.25mm
 3. CONTACT RATING: 50mA @ 12VDC
 4. CONTACT MATERIAL: SILVER
 - ▲ 5. OPERATING FORCE: 260± 50gf
 6. TRAVEL: 0.25 +0.2/-0.1mm
 7. CONTACT RESISTANCE: 100mΩ MAX.
 8. ELECTRICAL LIFE: 100,000 CYCLES
 9. PACKAGING: CARRIER IS FOLDED EVERY 25 PITCHES (24) SWITCHES PER FOLD.
 10. OPERATING TEMP: -40°C TO 85°C
 11. ▲ DENOTES CRITICAL PRAMETERS.

| REV | ECO NO | DESCRIPTION | DATE | BY |
|-----|------------|------------------------------------|----------|----|
| B | ECO-102541 | PRINT UPDATED TO CURRENT STANDARDS | 05/01/24 | JS |



OBJECT ID
000017894

| | | | | |
|-----------------|-----------|----|---------|-----|
| TITLE TL59F260Q | | | | |
| SCALE | DATE | DR | DWG | REV |
| 2:1 | 7/10/2000 | MM | P010584 | B |