




| ▲ SWITCH FUNCTION | |
|-------------------|-----------------------|
| POS. 1 | POS. 2 |
| | |
| 1-2 ON 3-4 OFF | 1-2 (OFF) 3-4 (ON) |

() = MOMENTARY



WHITE (FORWARD)
(+)
WHITE (REVERSE)
(-)

▲ SPDT ON (OFF) / OFF (ON)
CONTACT CONFIGURATION



NOTE:
1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERMINAL NUMBERS FOR REF. ONLY

4. RATING: 2A @ 48VDC
5. CONTACT RESISTANCE: 50mΩ MAX. @ 1A 12VDC
6. INSULATION RESISTANCE: 1,000MΩ @ 500VDC
7. DIELECTRIC STRENGTH: 2,000VAC MIN. FOR 1 MINUTE
8. ELECTRICAL LIFE: 50,000 CYCLES
9. OPERATING TEMPERATURE: -20°C to 55°C
10. INGRESS PROTECTION: IP65
11. ▲ DENOTES CRITICAL PARAMETER
12. ILLUMINATION COLOR: WHITE (FORWARD), WHITE (REVERSE)
13. ILLUMINATION VOLTAGE: 12V 20mA
14. HARDWARE INCLUDED: HEX NUT AND O-RING (NOT SHOWN)

E-SWITCH®

TITLE PV7F2Y0SS-304-M16

| | | | | | | | | |
|-------|--------|-------------|-----------|----|----|-----|--------------------|-----|
| SCALE | 1:1 | DATE | 6/25/2019 | DR | MW | DWG | 52-PV7F2Y0SS304M16 | REV |
| REV | PCR NO | DESCRIPTION | DATE | BY | | | | A |

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

| | | | | |
|-----|--------|------------------------|---------|----|
| A | 23941 | RELEASE FOR PRODUCTION | 6/25/19 | MW |
| REV | PCR NO | DESCRIPTION | DATE | BY |