



1. ALL DIMENSIONS IN MM [INCH]

2. GENERAL TOLERANCE: $X.X = \pm 0.4$

$$X.XX = \pm 0.25$$

3. TERMINAL NUMBERS FOR REF ONLY

▲ 4. CONTACT MATERIAL: SILVER

5. RATING: 3A 250 VAC cUL

6. ELECTRIC LIFE: 50,000 MAKE-AND-BREAK CYCLES AT FULL LOAD.

7. MECHANICAL LIFE: 500,000 CYCLES.

8. INSULATION RESISTANCE: 1,000 MΩ @ 500VDC MIN.

9. DIELECTRIC STRENGTH: 2,000 VAC MIN. FOR 1 MINUTE

10. CONTACT RESISTANCE: 50mΩ MAX. @ 1A 12VDC

11. OPERATING TEMP.: -20°C to 55°C

12. ▲ DENOTES CRITICAL PARAMETER.

▲ 13. LAMP VOLTAGE: 20mA 24V

14. TRAVEL: 3.2mm

15. ACTUATION FORCE: 2.5 ± 1.0 N

16 MOUNTING NUT TORQUE: 5-14 Nm

17. INGRESS PROTECTION: IP67

18. HARDWARE SUPPLIED: O-RING AND HEXNUT

REV	ECO NO	DESCRIPTION	DATE	BY	 E-SWITCH®					OBJECT ID
B	ECO-100359	UPDATE PANEL CUTOUT	12/09/21	JS						000026143
					TITLE ULV4F2311505					
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED					SCALE	DATE	DR	DWG	REV	
					3:2	12/18/2019	MW	T940143	B	