



GREEN (FORWARD)




GREEN (REVERSE)

SCHEMATIC
ON-ON
SPDT ILLUMINATED


 $17.60^{+.20}_{-.00}$
 $[\text{.69}^{+.008}_{-.000} \text{ in}]$


PANEL CUT-OUT
PANEL THICKNESS 1-10mm

 $\varnothing 19.00^{+.20}_{-.00}$
 $[\varnothing .748^{+.008}_{-.000} \text{ in}]$
 $\varnothing 15.50$
 $[\text{.61 in}]$

 $\varnothing 22.00$
 $[\text{.87 in}]$




▲ POWER SYMBOL
ILLUMINATION
COLOR: GREEN

▲ ACTUATOR
STAINLESS STEEL



NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERMINAL NUMBERS FOR REF ONLY
- ▲ 4. CONTACT MATERIAL: SILVER
5. RATING: 3A 250 VAC cUL
6. ELECTRIC LIFE: 50,000 MAKE-AND-BREAK CYCLES
AT FULL LOAD
7. MECHANICAL LIFE: 500,000 CYCLES
8. INSULATION RESISTANCE: 1,000 M Ω @ 500VDC MIN.
9. DIELECTRIC STRENGTH: 2,000 VAC MIN. FOR 1 MINUTE
10. CONTACT RESISTANCE: 50m Ω MAX. @ 1A 12VDC
11. OPERATING TEMP.: -20°C to 55°C
12. ▲ DENOTES CRITICAL PARAMETER
- ▲ 13. LAMP VOLTAGE: 20mA 12V
14. TRAVEL: 3.2mm
15. ACTUATION FORCE: 2.5 $\pm$ 1.0 N
16. MOUNTING NUT TORQUE: 5-14 Nm
17. INGRESS PROTECTION: IP67, IK10
18. HARDWARE SUPPLIED: O-RING AND HEXNUT



REV	ECO NO	DESCRIPTION	DATE	BY
B	ECO-100378	UPDATE PANEL CUTOOUT	12/10/21	JS



E-SWITCH®

OBJECT ID
000026142

TITLE ULV4F23SS534				
SCALE 3:2	DATE 12/4/2019	DR MW	DWG T940142	REV B

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED