






## NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X =  $\pm 0.4$   
 X.XX =  $\pm 0.25$
3. TERMINAL NUMBERS FOR REF ONLY
- ▲ 4. CONTACT MATERIAL: SILVER
5. RATING: 3A 250 VAC cUL
6. ELECTRIC LIFE: 50,000 MAKE-AND-BREAK CYCLES AT FULL LOAD.
7. MECHANICAL LIFE: 1,000,000 CYCLES.
8. INSULATION RESISTANCE: 1,000 M $\Omega$  @ 500VDC MIN.
9. DIELECTRIC STRENGTH: 2,000 VAC MIN. FOR 1 MINUTE
10. CONTACT RESISTANCE: 50m $\Omega$  MAX. @ 1A 12VDC
11. OPERATING TEMP.: -20°C to 55°C
12. ▲ DENOTES CRITICAL PARAMETER.
- ▲ 13. LAMP VOLTAGE: 20mA 6V
14. TRAVEL: 3.2mm
15. ACTUATION FORCE:  $2.5 \pm 1.0$  N
16. MOUNTING NUT TORQUE: 5-14 Nm
17. INGRESS PROTECTION: IP67
18. HARDWARE SUPPLIED: O-RING AND HEXNUT



| REV | ECO NO     | DESCRIPTION          | DATE     | BY | E-SWITCH®          |           |    |         | OBJECT ID |
|-----|------------|----------------------|----------|----|--------------------|-----------|----|---------|-----------|
| B   | ECO-100336 | UPDATE PANEL CUTOOUT | 12/09/21 | JS | TITLE ULV4F2B11343 |           |    |         | 000026052 |
|     |            |                      |          |    | SCALE              | DATE      | DR | DWG     | REV       |
|     |            |                      |          |    | 3:2                | 3/22/2016 | MW | T940050 | B         |

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO  
 E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED