




SWITCH	WIRE	LENGTH
SW1-1	WIRE, 24AWG AWM UL1015, WHITE	300.0 [11.8 in]
SW1-2	WIRE, 24AWG AWM UL1015, WHITE	300.0 [11.8 in]
SW1-3	WIRE, 24AWG AWM UL1015, YELLOW	300.0 [11.8 in]
SW1-4	WIRE, 24AWG AWM UL1015, YELLOW	300.0 [11.8 in]
SW1- (+)	WIRE, 24AWG AWM UL1015, RED	300.0 [11.8 in]
SW1- (-)	WIRE, 24AWG AWM UL1015, BLACK	300.0 [11.8 in]



RECOMMENDED PANEL CUTOUT
 MAX. PANEL THICKNESS 10.0 [.39 in]

NOTES:

1. DIMENSIONS IN MM [INCH]
2. TERMINAL NUMBERS FOR REF. ONLY
3. CONTACT MATERIAL: SILVER
4. RATING: 2A 48VDC
- ▲ 5. LAMP VOLTAGE: 12V
6. INGRESS PROTECTION: IP65
7. TRAVEL: 2.8mm
8. ACTUATION FORCE: 6.5N
9. OPERATING TEMP.: -20°C to 55°C
10. INSULATION RESISTANCE: 1,000 MΩ MIN.
11. CONTACT RESISTANCE: 50mΩ MAX. @ 1A 12VDC
12. DIELECTRIC STRENGTH: 2,000 VAC MIN. FOR 1 MINUTE
13. ELECTRIC LIFE: 50,000 CYCLES.
14. ▲ DENOTES CRITICAL PARAMETER.
15. ALL MATERIAL SHALL BE ROHS COMPLIANT
- ▲ 16. SUPPLIED HARDWARE: O-RING AND HEXNUT
17. USE P/N'S DESIGNATED OR ENGINEERING APPROVED EQUIVALENTS



REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
A	ECO-100470	RELEASE	10/25/21	JS	TITLE PV8FWT0SS-344-M14				100119869
					SCALE	DATE	DR	DWG	REV
					2:3	10/21/2021	JS	52-PV8FWT0SS344M14	A

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO
 E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED