


- NOTE:
1. ALL DIMENSIONS IN MM [INCH]
  2. GENERAL TOLERANCE: X.X = ±0.4  
X.XX = ±0.25
  3. TERMINAL NUMBERS FOR REF ONLY
  - ▲ 4. CONTACT MATERIAL: SILVER
  5. RATING: 3A 250 VAC cUL
  6. ELECTRIC LIFE: 50,000 MAKE-AND-BREAK CYCLES AT FULL LOAD.
  7. MECHANICAL LIFE: 500,000 CYCLES.
  8. INSULATION RESISTANCE: 1,000 MΩ @ 500VDC MIN.
  9. DIELECTRIC STRENGTH: 2,000 VAC MIN. FOR 1 MINUTE
  10. CONTACT RESISTANCE: 50mΩ MAX. @ 1A 12VDC
  11. OPERATING TEMP.: -20°C to 55°C
  12. ▲ DENOTES CRITICAL PARAMETER.
  - ▲ 13. LAMP VOLTAGE: 20mA 3V
  14. TRAVEL: 3.2mm
  15. ACTUATION FORCE: 3.5 ± 1.0 N
  16. MOUNTING NUT TORQUE: 5-14 Nm
  17. INGRESS PROTECTION: IP67, IK08
  18. HARDWARE SUPPLIED: O-RING AND HEXNUT



REV	ECO NO	DESCRIPTION	DATE	BY
A	ECO-101161	NEW RELEASE	08/05/22	MR



OBJECT ID  
100122515

TITLE ULV4F2GSLL41L17				
SCALE 1:1	DATE 8/4/2022	DR MJR	DWG T940407	REV A