


SCHEMATIC
ON - ON
DPDT Illuminated

$17.60^{+.20}_{-.00}$
[.69^{+.008}_{-.000} in]

PANEL CUT-OUT
PANEL THICKNESS 1-10mm

$\phi 19.00^{+.20}_{-.00}$
[$\phi 0.748^{+.008}_{-.000}$ in]

$\phi 15.50$
[.61 in]

$\phi 22.00$
[.87 in]

▲ POWER SYMBOL
ILLUMINATION: RED

▲ ACTUATOR
STAINLESS STEEL

▲ HOUSING
STAINLESS STEEL



2.0
[.08 in]

17.50 FLATS
[.69 in]

M19 x 1.0
THREAD

.50
[.02 in]

5.50
[.22 in]

13.00
[.51 in]

▲ 33.3
[1.31 in]

32.7
[1.29 in]

12.6
[.49 in]

17