



RECOMMENDED
PANEL CUT-OUT

▲ SCHEMATIC
OFF - (ON)
() DENOTES MOMENTARY FUNCTION

NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERMINAL NUMBERS FOR REF ONLY
4. CONTACT MATERIAL: SILVER PLATED
5. RATING: 2A 36VDC
6. ELECTRIC LIFE: 200,000
7. INSULATION RESISTANCE: 1,000MΩ MIN @ 500VDC.
8. DIELECTRIC STRENGTH: 2,000VAC MIN. FOR 1 MINUTE
9. CONTACT RESISTANCE: 50mΩ MAX. @ 1A 12VDC
10. OPERATING TEMP.: -20°C to 70°C
11. TRAVEL: 2.0mm
12. ▲ DENOTES CRITICAL PARAMETER.
13. ILLUMINATION COLOR: RED
14. HARDWARE SUPPLIED: O-RING AND HEXNUT (NOT SHOWN)
- ▲ 15. ILLUMINATION VOLTAGE RATING: 3V @ 20 mA
16. INGRESS PROTECTION: IP67



REV	ECO NO	DESCRIPTION	DATE	BY	TITLE PVA6FE24S13V			OBJECT ID
D	ECO-101215	TITLE PVA6FE24S11 TO PVA6FE24S13V	08/26/22	MR				000026216
					SCALE	DATE	DR	DWG
					2:1	9/20/2016	rc	T960006
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED					REV			D

 **E-SWITCH®**