






PANEL CUTOUT
MAX. PANEL THICKNESS 6mm

SWITCH FUNCTION	
POS. 1	POS. 2
OFF	ON
OPEN	1-2



- NOTE:
1. ALL DIMENSIONS IN MM [INCH]
 2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
 3. TERMINAL NUMBERS FOR REF ONLY
 4. CONTACT MATERIAL: SILVER
 5. RATING: 20A, 250VAC
25A, 30VDC
 6. ELECTRIC LIFE: 50,000 MAKE-AND-BREAK CYCLES
AT FULL LOAD.
 7. INSULATION RESISTANCE: 100M Ω @ 500VDC
 8. DIELECTRIC STRENGTH: 1,500 VAC
 9. CONTACT RESISTANCE: 100m Ω
 10. OPERATING TEMP.: -40°C to 85°C
 11. TRAVEL: 3.5mm
 12. ▲ DENOTES CRITICAL PARAMETER.
 - ▲13. LAMP VOLTAGE: 24V
 - ▲14. ILLUMINATION COLOR: GREEN
 - ▲15. INGRESS PROTECTION: IP67
 - ▲16. HARDWARE SUPPLIED: O-RING AND HEXNUT

REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
C	ECO-103050	UPDATE NOTE 5	10/31/24	JS					100128627
B	ECO-103047	NOTES 5 TO 25A, 30VDC, NOTE 10 TO -40 TO 85	10/24/24	JS	TITLE PVHC4F23SS635				
A	ECO-103037	RELEASE	10/17/24	JS					
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED					SCALE 3:2	DATE 10/16/2024	DR JS	DWG 52-PVHC4F23SS635	REV C