







SWITCH	WIRE	LENGTH
SW1-1 (C)	WIRE, 24AWG AWM UL1015, BLUE	300.0 [11.8 in]
SW1-2 (NO)	WIRE, 24AWG AWM UL1015, WHITE	300.0 [11.8 in]
SW1-3 (NC)	WIRE, 24AWG AWM UL1015, YELLOW	300.0 [11.8 in]
SW1-(+)	WIRE, 24AWG AWM UL1015, RED	300.0 [11.8 in]
SW1-(-)	WIRE, 24AWG AWM UL1015, BLACK	300.0 [11.8 in]





RECOMMENDED PANEL CUTOUT
MAX. PANEL THICKNESS 10.0 [.39 in]



NOTES:

1. DIMENSIONS IN MM [INCH]
2. ALL MATERIAL SHALL BE ROHS COMPLIANT
3. TERMINAL NUMBERS FOR REF. ONLY
4. CONTACT MATERIAL: SILVER
5. RATING: 2A 24VDC
6. INGRESS PROTECTION: IP65
7. TRAVEL: 2.8mm
8. OPERATING TEMP.: -25°C to 55°C
9. INSULATION RESISTANCE: 1,000 MΩ MIN.
10. CONTACT RESISTANCE: 50mΩ MAX. @ 1A 12VDC
11. DIELECTRIC STRENGTH: 2,000 VAC MIN. FOR 1 MINUTE
12. ELECTRIC LIFE: 50,000 MAKE-AND-BREAK CYCLES AT FULL LOAD.
13. ▲ DENOTES CRITICAL PARAMETER.
- ▲ 14. HARDWARE: O-RING AND HEXNUT SUPPLIED IN BULK IN A PLASTIC BAG.
- ▲ 15. USE PART NUMBERS DESIGNATED OR ENGINEERING APPROVED EQUIVALENTS
- ▲ 16. ILLUMINATION COLOR: RED / GREEN
- ▲ 17. ILLUMINATION VOLTAGE: 12V



A	24079	NEW RELEASE	10/29/19	MW
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE PVS7FW3SS-3G4-M01				
SCALE	DATE	DR	DWG	REV
2:3	10/29/2019	MW	52-PVS7FW3SS3G4M01	A