


GREEN (FORWARD)



GREEN (REVERSE)

SCHEMATIC





ON - (ON)

DPDT ILLUMINATED

() = MOMENTARY

NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERMINAL NUMBERS FOR REF ONLY
- ▲ 4. CONTACT MATERIAL: SILVER
5. RATING: 3A 250 VAC cUL
6. ELECTRIC LIFE: 50,000 MAKE-AND-BREAK CYCLES AT FULL LOAD.
7. MECHANICAL LIFE: 1,000,000 CYCLES.
8. INSULATION RESISTANCE: 1,000 M Ω @ 500VDC MIN.
9. DIELECTRIC STRENGTH: 2,000 VAC MIN. FOR 1 MINUTE
10. CONTACT RESISTANCE: 50m Ω MAX. @ 1A 12VDC
11. OPERATING TEMP.: -20°C to 55°C
12. ▲ DENOTES CRITICAL PARAMETER.
- ▲ 13. LAMP VOLTAGE: 20mA 24V
14. TRAVEL: 3.2mm
15. ACTUATION FORCE: 3.5 ± 1.0 N
16. MOUNTING NUT TORQUE: 5-14 Nm
17. INGRESS PROTECTION: IP67
18. HARDWARE SUPPLIED: O-RING AND HEXNUT

PANEL CUT-OUT
PANEL THICKNESS 1-10mm
 $\phi 19.00^{+0.20}_{-0.00}$
 $[\text{.748}^{+0.008}_{-0.000} \text{ in}]$
 $\phi 15.50$
 $[\text{.61 in}]$
 $\phi 22.00$
 $[\text{.87 in}]$
▲ RING ILLUMINATION
COLOR: GREEN▲ ACTUATOR
BLACK ANODIZED▲ HOUSING
STAINLESS STEEL

REV	ECO NO	DESCRIPTION	DATE	BY
B	ECO-100350	UPDATE PANEL CUTOOUT	12/09/21	JS

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

E-SWITCH®

OBJECT ID
000026091

TITLE ULV4F2HS1335				
SCALE 3:2	DATE 1/27/2017	DR MW	DWG T940091	REV B