




PARAMETERS	SYMBOL	MAX.	UNITS
LAMP VOLTAGE (VAC)	V	125	V
STARTUP VOLTAGE	V _s	95	V
CURRENT	I	0.8	mA
SERIES RESISTANCE (125V)	R	120	OHMS



PANEL THICKNESS	X dimension
0.75-1.25 [0.30-.049]	19.2-0.1 [7.56]
1.25-2.0 [0.49-.079]	19.4-0.1 [7.64]
2.0-3.0 [0.79-.118]	19.8-0.1 [7.80]



PANEL CUTOOUT
NOT TO SCALE

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25

$$X.XX=\pm 0.25$$



3. RATING: 6A @250VAC;9A @125VAC (UL, CSA, VDE)
4(1)A @250VAC
4. LAMP VOLTAGE: 125V (NEON BULB)
5. MATERIAL:

CONTACT SURFACE: Coin Silver, Silver Plate

6. CONTACT RESISTANCE: 20MILLIOHMS TYP. INITIAL TERMINAL: Copper Alloy W/ Silver Plate

7. INSULATION RESISTANCE: 1000Megaohms

8. DIELECTRIC STRENGTH: >1500V RMS min. @SEA LEVEL
>3000V RMS @SEA LEVEL
9. MECHANICAL LIFE: 50,000 CYCLES.
10. ELECTRICAL LIFE: 10,000 CYCLES.



TITLE			
R1973B BLK YEL EF1			
SCALE	DATE	DR	DWG
1.5:1	4/4/03	AR	M400040
REV			
A			