



PANEL CUTOUT

PANEL THICKNESS	(x)
0.75 - 1.25	30.0
1.25 - 2.00	30.4
2.00 - 3.00	30.7





SWITCH FUNCTION	
POS. 2	POS. 1
ON	ON
2-3	2-1



NOTE:

1. DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X ± 0.4
X.XX ± 0.25
3. TERMINAL NUMBERS FOR REF ONLY
4. CONTACT MATERIAL: SILVER
- ▲ 5. CONTACT RATINGS:
ANSI/UL 1054
16A @ 125VAC T65
16A @ 250VAC T65
6. CONTACT RESISTANCE: 20mΩ MAX. @ 50VAC INITIAL
7. INSULATION RESISTANCE: 100MΩ MIN. @ 500VDC
8. DIELECTRIC STRENGTH: 1,000VAC FOR 1 MINUTE
9. ELECTRICAL LIFE: 6,000 CYCLES [cURus]
10. OPERATING TEMPERATURE: 0°C to 65°C [cURus]
- ▲ 11. ILLUMINATION VOLTAGE: NON-ILLUMINATED
12. ▲ DENOTES CRITICAL PARAMETER



REV	ECO NO	DESCRIPTION	DATE	BY
C	ECO-101734	CORRECT TERMINAL CALLOUT	03/14/23	JS
B	ECO-101682	CORRECT SWITCH FUNCTION	02/27/23	JS



OBJECT ID
100123563

TITLE RB143E1200		SCALE 1:1	DATE 1/27/2023	DR JS	DWG 14-RB143E1200	REV C
---------------------	--	--------------	-------------------	----------	----------------------	----------