


WHITE (FORWARD)



▲ SCHEMATIC

ON - (ON)

DPDT ILLUMINATED

() DENOTES MOMENTARY FUNCTION

NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERMINAL NUMBERS FOR REF ONLY
- ▲ 4. CONTACT MATERIAL: SILVER
5. RATING: 3A 250 VAC cUL
6. ELECTRIC LIFE: 50,000 MAKE-AND-BREAK CYCLES AT FULL LOAD.
7. MECHANICAL LIFE: 1,000,000 CYCLES.
8. INSULATION RESISTANCE: 1,000 M Ω @ 500VDC MIN.
9. DIELECTRIC STRENGTH: 2,000 VAC MIN. FOR 1 MINUTE
10. CONTACT RESISTANCE: 50m Ω MAX. @ 1A 12VDC
11. OPERATING TEMP.: -20°C to 55°C
12. ▲ DENOTES CRITICAL PARAMETER.
- ▲ 13. LAMP VOLTAGE: 20mA 24V
14. TRAVEL: 3.2mm
15. ACTUATION FORCE: 3.5 $\pm$ 1.0 N
16. MOUNTING NUT TORQUE: 5-14 Nm
17. INGRESS PROTECTION: IP67, IK10
18. HARDWARE SUPPLIED: O-RING AND HEXNUT

PANEL CUT-OUT
PANEL THICKNESS 1-10mm
 $\phi 22.00^{+0.20}_{-0.00}$
[.866 $^{+0.008}_{-0.000}$ in]

 $\phi 25.00$
[.984 in]

 $\phi 17.75$
[.70 in]

 $\phi 13.75$
[.54 in]
▲ RING ILLUMINATION
COLOR: WHITE▲ ACTUATOR
STAINLESS STEEL▲ HOUSING
STAINLESS STEELM22 x 1.0
THREAD.50
[.020 in]5.50
[.22 in]13.00
[.51 in]

TERMINAL 3

TERMINAL 2

LED 1
(+)

TERMINAL 1

TERMINAL 6

LED 2
(-)

TERMINAL 5

TERMINAL 4

2.0
[.08 in]27.2
[1.07 in]▲ 35.0
[1.38 in]34.4
[1.35 in]5.00
[.197 in]2.80
[.110 in]10.00
[.394 in]

REV	ECO NO	DESCRIPTION	DATE	BY
B	ECO-100302	UPDATE PANEL CUTOOUT	09/27/21	JS

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

E-SWITCH®

OBJECT ID
000026346TITLE
ULV7F2HSS305SCALE
3:2DATE
9/24/2019DR
MWDWG
T970067REV
B