





BLUE (FORWARD)



▲ SCHEMATIC

ON - (ON)

DPDT ILLUMINATED

() DENOTES MOMENTARY FUNCTION

NOTE:

1. ALL DIMENSIONS IN MM [INCH]

2. GENERAL TOLERANCE: X.X = ± 0.4 X.XX = ± 0.25

3. TERMINAL NUMBERS FOR REF ONLY

▲ 4. CONTACT MATERIAL: SILVER

5. RATING: 3A 250 VAC cUL

6. ELECTRIC LIFE: 50,000 MAKE-AND-BREAK CYCLES
AT FULL LOAD.

7. MECHANICAL LIFE: 1,000,000 CYCLES.

8. INSULATION RESISTANCE: 1,000 M Ω @ 500VDC MIN.

9. DIELECTRIC STRENGTH: 2,000 VAC MIN. FOR 1 MINUTE

10. CONTACT RESISTANCE: 50m Ω MAX. @ 1A 12VDC

11. OPERATING TEMP.: -20°C to 55°C

12. ▲ DENOTES CRITICAL PARAMETER.

▲ 13. LAMP VOLTAGE: 20mA 220V






14. TRAVEL: 3.2mm

15. ACTUATION FORCE: 3.5 $\pm$ 1.0 N

16. MOUNTING NUT TORQUE: 5-14 Nm

17. INGRESS PROTECTION: IP67, IK10

18. HARDWARE SUPPLIED: O-RING AND HEXNUT

PANEL CUT-OUT
PANEL THICKNESS 1-10mm

REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
B	ECO-100301	UPDATE PANEL CUTOOUT	09/27/21	JS	TITLE ULV7F2HSS647				000026332
					SCALE	DATE	DR	DWG	REV
					3:2	10/11/2018	MW	T970053	B

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED