





SUGGESTED PANEL CUTOUT

SWITCH FUNCTION	
POS. 1	POS. 2
OFF	ON
OPEN	2-1, 2-3

CIRCUIT: SPST
OFF - ON

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERM. NOS. FOR REF. ONLY
- ▲ 4. RATING: 20A 125VAC [cURus]
16A 250VAC [cURus]
1/3HP 125/250VAC [cURus]
3/4HP 125/250VAC [cURus]
5. MATERIAL: CONTACT SURFACE: SILVER PLATED COPPER
TERMINAL: BRASS ALLOY w/SILVER PLATE
6. ELECTRICAL LIFE: 10,000 CYCLES MIN.
7. CONTACT RESISTANCE: 20 Milli-OHMS MAX.
8. OPERATING TEMP: -20°C TO 65°C [cURus]
-20°C TO 105°C [cURus]
9. DIELECTRIC STRENGTH: >1,000V AC 1MIN
- ▲ 10. LAMP VOLTAGE: 250V
11. ▲ DENOTES CRITICAL PARAMETER.



REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
C	ECO-100550	REMOVE VDE/ENEC RATING AND LOGO	02/03/22	JS	TITLE RSC241D1021-147				000000339
					SCALE	DATE	DR	DWG	REV
					1.5:1	10/19/2017	MW	14-RSC241D1021147	C

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED