








O.P. (MM)	P.T. (MM)
8.8 ± 0.8	1.6 Max.

O.P. = OPERATING POINT
P.T. = PRE-TRAVEL



NOTES:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
- ▲ 3. RATING: 3A @125VAC
1.5A @250 VAC UL
- ▲ 4. OPERATING FORCE: 15 ± 10 GRAMS
- OPERATING TEMP: -25°C to 75°C
- ELECTRICAL LIFE: 10,000 CYCLES MIN.
- MECHANICAL LIFE: 1,000,000 CYCLES
- INSULATION RESISTANCE: 100 MEGA-OHMS MIN.
- DIELECTRIC STRENGTH: 500VAC - 1 MINUTE
- ▲ DENOTES CRITICAL PARAMETER.
- PACKAGED IN TRAYS, 120 PIECES PER TRAY



REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
F	ECO-102005	PRINT UPDATE	06/16/23	JS	TITLE SS0750301F015V1A				000021317
					SCALE	DATE	DR	DWG	REV
					4:1	6/24/2008	BLR	Q971001	F

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED