


O.P. (MM)	P.T. (MM)
8.8 ±0.8	1.6 MAX.




O.P. = OPERATING POINT
P.T. = PRE-TRAVEL



CIRCUIT: SPDT

NOTES:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: X.X=± 0.4
X.XX=± 0.25
- ▲ 3. RATING: 3A @ 125 VAC
1.5A @ 250VAC UL
- ▲ 4. OPERATING FORCE: 40± 15 GRAMS
5. OPERATING TEMP: -25°C TO 75°C
6. ELECTRICAL LIFE: 10,000 CYCLES MIN.
7. INSULATION RESISTANCE: 100 MEGA-OHMS MIN.
8. DIELECTRIC STRENGTH: 500VAC - 1 MINUTE
- ▲ 9. DENOTES CRITICAL PARAMETER.
10. PACKAGED IN TRAYS, 120 PIECES PER TRAY.



REV	ECO NO	DESCRIPTION	DATE	BY
D	ECO-102030	PRINT UPDATE	07/03/23	JS



E-SWITCH®

OBJECT ID
000021330

TITLE SS0750301F040S1A

SCALE
4:1

DATE
6/24/2008

DR
BLR

DWG
Q971014

REV
D

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED