




RECOMMENDED PANEL CUT OUT
MAX. PANEL THICKNESS: 5mm



▲ SWITCH FUNCTION		
POS. 1	POS. 2	POS. 3
(ON)	OFF	(ON)
2-3	OPEN	2-1

(ON) = DENOTES MOMENTARY




Ø6.00
[Ø.236 in]

▲ M12 X 1.0
(HARDWARE
NOT SHOWN)

Ø2.60
[Ø.102 in]

Ø4.20
[Ø.165 in]



NOTES:

1. ALL DIMENSIONS IN MM
2. GENERAL TOLERANCE: X.X = ±0.5
X.XX = ±0.25
3. TERM. NOS. FOR REFERENCE ONLY
4. ELECTRICAL LIFE: 6,000 CYCLES
5. OPERATING TEMP: 0°C to 85°C
6. CONTACT RESISTANCE: 50mΩ MAX. INITIAL
7. INSULATION RESISTANCE: 2MΩ AT 500VDC
8. DIELECTRIC STRENGTH: 1000VAC FOR 1 MINUTE
9. ▲ DENOTES CRITICAL PARAMETER
10. CONTACT RATING: 20A 125VAC,
15A 277VAC
1.5HP 125/277VAC
- ▲ 11. SUPPLIED HARDWARE: 2 HEXNUTS

REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
B	ECO-101967	release print	05/26/23	MW	TITLE ST12DD00				000001065
					SCALE	DATE	DR	DWG	REV
					1:1	5/23/2023	MW	34-ST12DD00	B

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED