




RECOMMENDED PANEL CUT OUT




| ▲ SWITCH FUNCTION |        |        |
|-------------------|--------|--------|
| POS. 1            | POS. 2 | POS. 3 |
|                   |        |        |
| (ON)              | OFF    | (ON)   |
| 2-3               | NONE   | 1-2    |

( ) = DENOTES MOMENTARY



## NOTES:

1. ALL DIMENSIONS IN MM
2. GENERAL TOLERANCE: X.X =  $\pm 0.5$   
X.XX =  $\pm 0.25$
3. TERM. NOS. FOR REFERENCE ONLY
4. ELECTRICAL LIFE: 6,000 CYCLES
5. OPERATING TEMP: 0°C to 85°C
6. CONTACT RESISTANCE: 50mΩ MAX. INITIAL
7. INSULATION RESISTANCE: 2MΩ AT 500VDC
8. DIELECTRIC STRENGTH: 1000VAC FOR 1 MINUTE
9. ▲ DENOTES CRITICAL PARAMETER
10. CONTACT RATING: 20A 125VAC,  
15A 277VAC  
1.5HP 125/277VAC
- ▲ 11. SUPPLIED HARDWARE: 2 HEXNUTS



E-SWITCH®

OBJECT ID  
000001078

|     |        |                                |         |     |
|-----|--------|--------------------------------|---------|-----|
| B   | 24486  | DRAWING UPDATE CAD TO INVENTOR | 9/14/20 | MJR |
| A   | 19197  | INITIAL RELEASE                | 7/19/10 | CAB |
| REV | PCR NO | DESCRIPTION                    | DATE    | BY  |

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO  
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

|                |                  |           |                    |          |
|----------------|------------------|-----------|--------------------|----------|
| TITLE ST14DD10 |                  |           |                    |          |
| SCALE<br>2:3   | DATE<br>8/5/2009 | DR<br>CAB | DWG<br>34-ST14DD10 | REV<br>B |