








RECOMMENDED PCB LAYOUT



NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. RATING: 12VDC, 50mA MAX.
4. CONTACT RESISTANCE: 500m Ω MAX.
5. INSULATION RESISTANCE: 100M Ω MIN. @ 100VDC
6. TRAVEL: 0.2 $\pm$ 0.1mm
7. DIELECTRIC STRENGTH: 250V AC FOR 1 MIN.
- ▲ 8. OPERATING FORCE: 160 $\pm$ 50gf
9. OPERATING TEMPERATURE: -40°C to 85°C
10. OPERATING LIFE: 100,000 CYCLES
11. PACKAGING: TAPE & REEL, 1400 PIECES PER REEL
12. ▲ DENOTES CRITICAL PARAMETER
- ▲ 13. CONTACT MATERIAL: SILVER PLATED



LED SPECS	UNITS	YELLOW	WHITE
FORWARD CURRENT	mA	20	20
FORWARD VOLTAGE	V	2.00 typ.	3.30 typ.
LUMINOUS INTENSITY	mcd	300 typ.	600 typ.
PEAK WAVELENGTH	nm	590	N/A

REV	ECO NO	DESCRIPTION	DATE	BY
B	ECO-103681	Print update	10/03/25	MW

 E-SWITCH®		OBJECT ID	
		100125509	
TITLE TL3275AF160YWQ			
SCALE	DATE	DR	DWG
8:1	8/22/2023	JS	B327512
			REV
			B

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED