











NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: $x.x \pm 0.4\text{mm}$
 $x.xx \pm 0.25\text{mm}$
3. RATING: DC 30V, 0.3A
4. OPERATING FORCE: $200 \pm 100\text{gf}$
5. TRAVEL: FULL: 3.3mm, LOCK: 2.5mm
6. LIFE CYCLES: 10,000 CYCLES
7. OPERATING TEMPERATURE: -20°C TO 70°C
8. CONTACT RESISTANCE: $20\text{m}\Omega$ MAX.
9. INSULATION RESISTANCE: $100\text{M}\Omega$ MIN@ 500VDC.
- ▲ 10. LED COLOR: RED/BLUE
11. ▲ DENOTES CRITICAL PARAMETER.
12. 2002/95/EC (RoHS) COMPLIANT.
13. PACKAGING: 100 PIECES PER TRAY



▲ R05 BUTTON
TRANSPARENT
(B410000)



LED SPECS	UNITS	RED	BLUE
FORWARD CURRENT	mA	20	20
FORWARD VOLTAGE @20mA	V	1.95 Typ-2.5 Max	3.3 Typ-4 Max
LUMINOUS INTENSITY @ 20mA	MCD	400 TYP	60 TYP



TITLE WBL2UEERBQR05CLR

B	21659	ADDED NOTE 13	10/23/14	AS
A	20616	INITIAL RELEASE	05/22/12	drg
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

DATE 5/22/2012

DR drg

DWG XB0933P

REV B