










NOTES:

1. ALL DIMENSIONS IN MM
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERM. NUMBERS FOR REFERENCE ONLY.
4. CONTACT RATING: 0.1A Max. @ 28VDC
- ▲ 5. CONTACT MATERIAL: SILVER
6. ELECTRICAL LIFE: 200,000 Typical
7. MECHANICAL LIFE: 1,000,000 CYCLES TYP.
8. OPERATING TEMP: -40°C to +85°C
9. OPERATING FORCE: 200 ± 100 gf
10. CONTACT RESISTANCE: 100 MILLI-OHM INITIAL TYP. MAX.
11. DIELECTRIC STRENGTH: 1000 VAC FOR 1 MINUTE
12. TRAVEL TO MAKE: 2.20 ± 0.2 mm
13. ▲ DENOTES CRITICAL PARAMETER
- ▲ 14. LED COLOR: RED: 1 CHIP, 2.1-2.5 VDC@20mA
GRN: 1 CHIP, 3.2-4.0 VDC@20mA
BLU: 1 CHIP, 3.1-3.8 VDC@20mA



REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
A	ECO-101264	Release	09/22/22	MW	TITLE ULP12OAP1QLSCL1RGB				100122750
					SCALE	DATE	DR	DWG	REV
					3:2	9/19/2022	MW	B800088	A

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED