



SERPAC 151R

ELECTRONIC ENCLOSURES







PART NO.	DESCRIPTION (Included)	ACCESSORIES (Optional)	
5-1R	Top	PART NO.	DESCRIPTION
15	Bottom	50	Non-skid Feet
6017	4-40 x 1" Screw (4)	PS15	Waterproof Perimeter Seal
6102	4-40 Threaded Inserts (4)	1030	Pocket Clip
		1040	2AA Battery Holder
		55	Key Holder
		60	Standoff Hole
		61	Standoff Post


Notes: Enclosure weight .25 lb / 112 g
1) Enclosure meets or exceeds IP40 and NEMA 1
2) Circuit Board drawings see sheet 3.
3) All components are RoHS Compliant.
4) Material: Top and Bottom ABS.
5) When used with PS15 the enclosure meets or exceeds IP 67 and NEMA 4X, 12 and 13 MIL-STD-810G 506.5 (.02 lb / 11g)

SERPAC 151R

ELECTRONIC ENCLOSURES



- Notes:
- 1) Enclosure meets or exceeds IP40 and NEMA 1
 - 2) Circuit Board drawings see sheet 3.
 - 3) All components are RoHS Compliant.
 - 4) Material: Top and Bottom ABS.
 - 5) Customizable molding areas. $\triangle 5$
 - 6) PCB Bosses accept #4 self tapping screw. $\triangle 6$
 - 7) When used with PS15 the enclosure meets or exceeds IP 67 and NEMA 4X, 12 and 13 MIL-STD-810G 506.5 (.02 lb / 11g)



SERPAC 151R CIRCUIT BOARD

ELECTRONIC ENCLOSURES

Top & Bottom Option

